


Metered Rack PDU

Outlets. The PDU has eight (8) NEMA 5-15 outlets.

Digital display. A digital display shows aggregate current being used per phase by the PDU.

Power cord. The 12-ft (3.65-m) power cord terminates with a NEMA 5-15P connector.

AD-108-515-15A-515



Specifications

Electrical

Input connector	NEMA 5-15P
Cord length	12 ft (3.65 m)
Nominal input voltage	120 V
Input frequency	50–60 Hz
Acceptable input voltage	±10% of nominal voltage
Maximum input current total (phase)	12 A
Nominal output voltage	120 V
Maximum output current (outlet)	12 A
Output connectors	(8) NEMA 5-15

Physical

Dimensions (H × W × D)	1.74 × 17.47 × 4.03 in (4.41 × 44.37 × 10.23 cm)
Shipping dimensions (H × W × D)	2.50 × 18.50 × 13.25 in (6.35 × 46.99 × 33.65 cm)
Weight	3.80 lb (1.41 kg)

Environmental

Elevation (above MSL)	
Operating	10,000 ft (3000 m)
Storage	50,000 ft (15 000 m)
Temperature	
Operating	23 to 113°F (–5 to 45°C)
Storage	–13 to 149°F (–25 to 65°C)
Humidity	
Operating	5–95%, non-condensing
Storage	5–95%, non-condensing

Approvals

Safety Certification	UL/C-UL listed to UL/CSA 60950, DENAN approved
Emissions	FCC Class A, ICES-003, VCCI
