



Specification

Input Interface :

Front I/O:

- DVI : 1 x HDMI, up to 3840x2160@60Hz
- DP : 1 x Display Port, up to 3840x2160@60Hz

Rear I/O:

- VGA : 1 x VGA, up to 1920x1080@60Hz
- DVI : 1 x DVI-D, up to 3840x2160@60Hz
- HDMI : 1 x HDMI, up to 1920x1080@60Hz
- Power Input : 1 x DC input

Power Specification:

- Power Adapter : N/A
- Consumption : 85 W typical, normal operation
- Input : 12V DC Input w/external AC to DC power adapter
- Power Cord : 1 x Power Cord

Panel Specification :

- Size/ Type : 27" LCD (LED backlight)
- Active Area (mm) : 596.16 (H) x 335.34 (V)
- Pixel Pitch (um) : 155.25 (H)x 155.25 (V)
- Resolution : 3840 x 2160 @ 60Hz
- Contrast Ratio : 1000 : 1 (typ.)
- Max. Colors : 1.07B colors
- Brightness : 400 nits (cd/m²)
- Viewing Angle : -89 ~ 89 (H); -89 ~ 89 (V)
- Response Time : 12 m sec.(typ.)

OSD :

- OSD Input : 4 -key OSD buttons
- OSD Function : Contrast, Color, Position, Auto-adjustment, Factory Settings

Environment Tolerance:

- Operating Temperature : 0 deg. C to 50 deg. C
- Storage Temperature : -20 deg. C to 70 deg. C

Order Information :

- Speaker : 2W Speaker x2 (optional)

Drawings

