

ID-HE21Aw 21" Full HD High Brightness Widescreen LCD Panel w/ LED-backlit Display



**NEMA 4 / IP65
front protection**




Display Benefits

- ▶ 21.5" widescreen LCD with high brightness 1000 cd/m², **Full HD** 1080p resolution
- ▶ PIP & Picture by Picture viewing efficiency
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ 6mm aluminum front bezel with protective glass & water proof sealed gasket


Options

- 3G / HD / SD-**SDI** Broadcast-grade input
- **MC** Multi-display control solution
- 21" Touchscreen : Capacitive, Resistive, 2-point touch
- S-Video + Composite (BNC) or Audio input
- MIL-type or lockable connector
- 48V, 24V or 12VDC power
- TV - Analog
- Auto / switch dimming

Basic I/O



AV3.0 upgrade I/O with advanced features



Specifications

• LCD Panel

Size (diagonal) :	21.5" Widescreen TFT
Max resolution :	1920 x 1080
Brightness (cd/m ²) :	1000
Backlight :	LED
Colors :	16.7 M
Contrast ratio (typ) :	5000 : 1
Viewing angle (H/V) :	178° x 178°
Active area (mm) :	477 x 268
MTBF (hrs) :	50,000
Signal input :	VGA, DVI-D and HDMI

• Weight

Net : 6.9 kgs (15.2 lbs)

• Mounting :

Panel mount / VESA mount

• Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• Casing Color :

Black front panel (RAL 9005)
Dark grey rear case (RAL 7037)

• Regulatory :

FCC, CE

• Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 84 Watt, Standby 5 Watt

• Dimensions

Product : 577.8 x 59.1 x 369.3 mm / 22.7 x 2.3 x 14.5 inch

Diagrams (mm)

