




Features


- Support combo interface, VGA-USB & VGA-PS/2.
- Additional one USB Local console to add local KB/Mouse & VGA.
- Durable 104-key keyboard and touch pad.
- Quick and simple installation.
- Self-locking and auto release rails for ultra-convenience.
- Port selection via push buttons or On-Screen-Display (OSD).
- Dedicated daisy chain port to expand up to 240 servers



Rear of LCD1U19-17



Rear of LCD1U19-17-8KVM



Rear of LCD1U19-17-16KVM

Part No.	LCD1U19-17	LCD1U19-17-8KVM	LCD1U19-17-16KVM
Direct no. of Computers	1	8	16
Maximum no. of Computers	1	232(Daisy Chain)	240(Daisy chain)
LCD	Size	19"	
	Backlight	LED	
	Resolution	1280*1024	
	Max. color	16.7M	
	Luminance	250cd/m2	
	View Angel (H/V)	170 / 160	
	Contrast Ratio	1000 : 1	
Port Selection	N/A		Push Button, OSD or Hotkey
USB Local console	Yes , USB x2 for KB/ Mouse , VGA x1		
KB/Mouse Emulation	USB & PS2		
Rack Depth	500mm to 1100mm (rack cabinet front rails to rear rails)		
Power	100-240V AC 50/60Hz via IEC Type power cord		
Environment	Operation temp: 0 to 50°C Storage temp: -20 to 60°C Humidity: 10% - 90%, non-condensing Shock: 10G acceleration (11ms duration) Vibration: 17 to 500Hz 1G PTP		

Physical Dimensions / Net Weights

448x42x580mm (WxHxD) / 12.5KG