



-7L: 7 x Low Profile PCI Slots

- EIA RS-310C 19" Rackmount Standard
- Construction: Heavy Duty Cold Rolled Electroplated Steel
- Color: Black (Standard) or Custom
- System Boards: Intel or AMD
- Support ATX M/B (Max. to 12" x 9.6")
- Drive Capacity: 1x 5.25" & 1x Slim FDD & 3x 3.5" HDD
- Power Supply (Optional): 1U Single ATX P/S (Rear Installation) Max. Depth 205mm
- Cooling: 1x (80mm = 42.5CFM ea.) & 2x (40 x 20mm = 7CFM ea) Fans
- Riser Card: (Optional)
- Connector Port (Front): 2x USB Ports
- Expansion Slots(Optional): 3x Horizontal ISA/PCI/AGP Option Slots or 7x Low Profile PCI Slots
- Indicators: LEDs for Power ON/OFF, LAN, HDD Activity
- Switch: Power ON/OFF Momentary(Square), System Reset
- Dimensions (WxHxD): 483x88x355mm (19" x 3.5" x 13.9")
- Cuft: 2.0
- Humidity: 5% - 95% Non-condensing

