



(USB Port for single-port model only)




Features


- KVM switch supports combo interface, VGA-USB & VGA-PS2
- Short depth design suit for mobile rack and limited space.
- Durable 88-key keyboard and touch pad.
- Quick and simple installation.
- Self-locking and auto release rails for ultra convenience.
- Port selection via push buttons or On-Screen-Display (OSD).
- Dedicated daisy chain port to expand up to 240 servers.

Options

- 8-port or 16-port KVM switch (Front & Rear USB will be removed when adding KVM switch)
- Composite Video input
- HDMI or Display Port input
- 3G / HD / SD SDI Broadcast grade input
- 48V, 24V or 12V DC Power



Rear of LCD1U15-17-8KVM



Rear of LCD1U15-17-16KVM

Part No.	LCD1U15-17-8KVM	LCD1U15-17-16KVM
Direct no. of Computers	8	16
Maximum no. of Computers	232(Daisy Chain)	240(Daisy chain)
LCD	Size	17.3"
	Backlight	LED
	Resolution	920*1080 Full HD (support resolution up to 1920x1200)
	Max.color	262K
	Luminance	300cd/m2
	View Angel (H/V)	140 / 120
	Contrast Ratio	650 : 1
Port Selection	Push Button,OSD or Hotkey	
USB Local console / Expansion Slot	N/A	
KB/Mouse Emulation	USB & PS2	
Rack Depth	380mm to 620mm (rack cabinet front rails to rear rails)	
Power	100-240V AC 50/60Hz via IEC Type power cord	
Environment	Operation temp: 0 to 50°C	
	Storage temp: -20 to 60°C	
	Humidity: 10% - 90%, non-condensing	
	Shock: 10G acceleration (11ms duration) Vibration: 17 to 500Hz 1G PTP	
Physical Dimensions / Net Weights	443x42x457.2mm (WxHxD) /14KG	