




Features

- Dual slide rail capable LCD screen and keyboard tray independent operate.
- 1U 17.3 inch widescreen LCD Console Drawer
- DVI & VGA Port
- 1920 x 1080 high resolution
- Support FHD with 1080p resolution.
- Front 1xUSB, Rear 2xUSB 2.0 Type A, Sharing USB peripheral Device for computer (ex, flash disk, hard driver, KB/Mouse)
- 104-key keyboard with touch pad mouse.
- USB 2.0 Keyboard & Mouse
- Self-locking and auto release rails for ultra convenience.
- Build in 2x 2 watts speakers

Options

- Composite Video input
- HDMI or Display Port input
- 3G / HD / SD –SDI Broadcast grade input
- 48V, 24V or 12V DC Power



Rear of LCD1U17-48

Part No.		LCD1U17-48
Direct no. of Computers		1
KVM Connectors		DVI-D, VGA, USB
LCD	Size	17.3"
	Backlight	LED
	Resolution	1920*1080 Full HD (support resolution up to 1920x1200)
	Max.color	262K
	Luminance	300cd/m2
	View Angel (H/V)	140 / 120
Contrast Ratio		650 : 1
USB HUB		1x Front , 2x Rear USB 2.0 Type A for peripheral USB devices
Touch Screen		YES , for option (Driver needed)
KB/Mouse Emulation		USB 2.0
Audio		1 x 3.5 mm audio jack
Rack Depth		500mm to 1100mm (rack cabinet front rails to rear rails)
Power		100-240V AC 50/60Hz via IEC Type power cord
Environment		Operation temp: 0 to 50°C Storage temp: -20 to 60°C Humidity: 10% - 90%, non-condensing Shock: 10G acceleration (11ms duration) Vibration: 17 to 500Hz 1G PTP
Physical Dimensions / Net Weights		482x44.4x685mm (WxHxD) / 13.0KG