



Introduction

LCDK1001-b is the slimmest keyboard drawer which houses a compact 87-key keyboard with trackball mouse. There is cable guide for holding the keyboard and mouse cable for smooth operation.

Features

- Smart and compact design for rack-mount application
- 1U (1.75") height to save space
- Equipped with 87-key keyboard and trackball mouse

Part No.	LCDK1001-b
Physical Dimension (W x H x D)/Net Weight	483 x 44 x 340 mm / 6.5 KG
Construction	Heavy-duty steel
Color	black
No. of Keys	87
Rack Depth	340mm to 650mm ( rack cabinet front rails to rear rails )
Interface	USB
LED	Num. Cap. Scroll Lock
MTBF	10 million strokes
Safety	CE / FCC / RoHs
Operating Temp	0° ~ 50°C
Storage Temp	-10° ~ 60°C
Operating Humidity	5% ~ 95%, Non-condensing
Storage Humidity	5% ~ 95%

