



- Commercial grade monitor in a steel frame
- Mounts flush in 8U (14.0") of vertical 19" rack space
- 19" LCD display with 1280 x 1024 resolution
- Steel front panel construction with a durable powder coat finish
- LED Backlight provides high contrast ratios and energy savings
- Analog and Digital inputs
- IPS Display features wide H/V viewing angles

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 14.0" (H) x 2.0" (D)

Weight:

9 lbs.

Power:

100 - 240 VAC, 50/60 Hz.
18 Watts typ.

On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical
Position, Auto Adjust, OSD H & V Position, Input Select
Color Temp., Reset.

Temperature:

Operating: 0°C to 40°C
Storage: -20°C to 60°C

Humidity:

Operating: 20-90% RH

Input Signal (VGA):

R.G.B. analog video.

Input Signal (Digital):

DVI-D

Input Connectors:

Analog: 15-pin mini D-Sub.
Digital: DVI-D

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

IPS

Display area:

19.0" Diagonal.

Colors Displayed:

16.7 million colors.

Contrast Ratio:

1000:1

Brightness:

250 cd/m² typ.

Backlight:

LED

Viewing Angle:

Horizontal: 178°
Vertical: 178°

Response Time:

14ms

Resolution:

VGA up to 1280 x 1024.

Horizontal Frequency:

24 to 82 KHz.

Vertical Frequency:

50 to 75 Hz.

Specifications subject to change without notice.