

# RK1008 2U Rack Mount Speaker



## 2U Rack Mount Speaker

The Rk1008 speaker system offers improved sound quality via polypropylene drivers vs paper drivers. This fully enclosed amplified stereo speaker system has front panel controls which include a Power ON/OFF and Volume Control Switch with Power Indicator. The front panel Headphone Jack disables the internal speakers when a headphone plug is inserted, directing audio output to the headphones. A front panel 3.5mm AUX input jack overrides the rear input source allowing connection of a second source. The unit is supplied with a detachable audio cable and an external 110 VAC 60 Hz input power supply (optional 110/220 VAC 50/60 Hz input power supply).



Rear View - 110VAC Power Supply



Rear View - 110/220VAC Power Supply

## GENERAL SPECIFICATIONS

### Dimensions:

19.0" (W) x 3.5" (H) x 3.5" (D)

### Weight:

4.7 lbs

### Power Supply:

Standard - 110 VAC, 60 Hz.

Optional - 110/220 VAC, 50/60 Hz.

### Colors Available:

Black.

### Front Panel Controls:

Power ON/OFF plus Volume Control switch with Power Indicator, Headphone and Auxillary Input Jacks.

### Audio Amplifier Output:

12 Watts.

### Audio Input Connector:

1/8" (3.5mm) stereo jack.

Specifications subject to change without notice.



We offer OEM and custom solutions.  
Contact us for additional information.