

4U iSeries Injection Molded Fly Rack - 13"

Part Number 3i-2217M124U



FEATURES

SPECIFICATIONS

Exterior	Hard	-
Built In Wheels or Casters	Yes	-
Rack Units	4	-
Rail To Rail	12.75 in	32.38 cm
Front Wall To Rail	2 in	5.08 cm
Right Wall To Rail	1.375 in	3.49 cm
Left Wall To Rail	1.375 in	3.49 cm
Back Wall To Rail	2 in	5.08 cm
Acc Slot Length	14.75 in	37.47 cm
Acc Slot Width	10 in	25.40 cm
Acc Slot Height	1.75 in	4.45 cm
Product Weight	28.59 lb	12.97 kg
Carton Length	25.5 in	64.77 cm

Carton Width	20 in	50.80 cm
Carton Height	15 in	38.10 cm

AVAILABLE CONFIGURATIONS

3i-2217M124U	Black	-
--------------	-------	---