

6U iSeries Injection Molded Fly Rack - 13"

Part Number 3i-2317M146U



FEATURES

SPECIFICATIONS

Exterior	Hard	-
Built In Wheels or Casters	Yes	-
Rack Units	6	-
Rail To Rail	12.75 in	32.38 cm
Front Wall To Rail	1.825 in	4.64 cm
Right Wall To Rail	1.75 in	4.45 cm
Left Wall To Rail	2 in	5.08 cm
Back Wall To Rail	2.125 in	5.40 cm
Acc Slot Length	14.5 in	36.83 cm
Acc Slot Width	9.25 in	23.50 cm
Acc Slot Height	0.5 in	1.27 cm
Product Weight	31.17 lb	14.14 kg
Carton Length	26.5 in	67.31 cm

Carton Width	20 in	50.80 cm
Carton Height	16.5 in	41.91 cm

AVAILABLE CONFIGURATIONS

3i-2317M146U	Black	-
--------------	-------	---