

NOTE:  
22.5 MAX RAIL TO RAIL  
12.5 MIN RAIL TO RAIL

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/8$   
ANGULAR: BEND  $\pm 1$  DEGREE  
TWO PLACE DECIMAL  $\pm .03$   
THREE PLACE DECIMAL  $\pm .01$

Surface Area

MATERIAL

FINISH

APPLICATION


DO NOT SCALE DRAWING

	NAME	DATE
DRAWN		
CHECKED		
ENG APPR.		
MFG APPR.		
Q.A.		
COMMENTS:		

**Synergy Global Technology Inc**  
[www.RackmountMart.com](http://www.RackmountMart.com)

TITLE:  
**9U LINIER WM SWINGOUT  
CABINET- GLASS DOOR**

SIZE	DWG. NO.	REV
<b>A</b>		
SCALE: 1:10	WEIGHT: 48.26	SHEET 1 OF 2



UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN INCHES  
 TOLERANCES:  
 FRACTIONAL  $\pm 1/8$   
 ANGULAR: BEND  $\pm 1$  DEGREE  
 TWO PLACE DECIMAL  $\pm .03$   
 THREE PLACE DECIMAL  $\pm .01$

Surface Area	
MATERIAL	
FINISH	
NEXT ASSY	USED ON
APPLICATION	
DO NOT SCALE DRAWING	

	NAME	DATE
DRAWN		
CHECKED		
ENG APPR.		
MFG APPR.		
Q.A.		
COMMENTS:		

**Synergy Global Technology Inc**  
[www.RackmountMart.com](http://www.RackmountMart.com)

TITLE:  
**9U LINIER WM SWINGOUT  
 CABINET- GLASS DOOR**

SIZE	DWG. NO.	REV
<b>A</b>		
SCALE: 1:10	WEIGHT: 48.26	SHEET 2 OF 2