


PDU specification drawing

3-Phase 400V 32A basic PDU : UK x 18



32A model :	Fuse	MCB
VP18UK135-32A-W/CR_EN/2B-1	-	6

- Input Rating : 32A, 400V
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
 Protection : 16A single pole hydraulic MCB x 6
 Bank Details : **PH-1** < **Bank 1** > Output 16A max. U K # 1 - 3
 < **Bank 2** > Output 16A max. U K # 4 - 6
PH-2 < **Bank 3** > Output 16A max. U K # 1 - 3
 < **Bank 4** > Output 16A max. U K # 4 - 6
PH-3 < **Bank 5** > Output 16A max. U K # 1 - 3
 < **Bank 6** > Output 16A max. U K # 4 - 6

Three phase basic PDU
 Outlet : 13A Rated BS1363 x 18



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
 Copyright 2015 Synergy Global Technology Inc. All rights reserved.

EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1650 (H) mm
 Material : Extrusion
 Color : Black