



16A model :	Fuse	MCB
VP21C13/3C19-16A-CR_EN/2B-1	-	3

Input Rating : 16A, 400V  
 Inlet : 16A IEC60309 3P+N+E 6hr Red plug  
 Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset  
 Protection : 16A single pole hydraulic MCB x 3  
 Phase Details : < PH-1 > Output 16A max. C 13 # 1-7 + C 19 # C 1  
 < PH-2 > Output 16A max. C 13 # 1-7 + C 19 # C 1  
 < PH-3 > Output 16A max. C 13 # 1-7 + C 19 # C 1

### Three phase basic PDU

Outlet : 10A Rated IEC320 C13 x 21  
 16A Rated IEC320 C19 x 3



EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1650 (H) mm  
 Material : Extrusion  
 Color : Black