


3-Phase 400V 32A individual fused switched PDU : C13 x 36 + C19 x 12



| 32A model : | Fuse | MCB |
|------------------------------------|------|-----|
| VP36C13/12C19-32A-WS/GF/F_EN/2B-2 | 6 | - |
| VP36C13/12C19-32A-WS/GF/CR_EN/2B-2 | - | 6 |

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details :
 - PH-1 < Bank 1 >** Output 16A max. C13 #1-11 (odd) + C19 #C1, C3
 - < Bank 2 >** Output 16A max. C13 #2-12 (even) + C19 #C2, C4
 - PH-2 < Bank 3 >** Output 16A max. C13 #1-11 (odd) + C19 #C1, C3
 - < Bank 4 >** Output 16A max. C13 #2-12 (even) + C19 #C2, C4
 - PH-3 < Bank 5 >** Output 16A max. C13 #1-11 (odd) + C19 #C1, C3
 - < Bank 6 >** Output 16A max. C13 #2-12 (even) + C19 #C2, C4

Three phase switched PDU

Outlet : 10A Rated IEC320 C13 with 5A individual fuse x 36
16A Rated IEC320 C19 with 5A individual fuse x 12



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (WS Switched PDU)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
- Outlet Control : Outlet Switch ON / OFF
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 90 (D) x 1925 (H) mm
- Material : Steel
- Color : White (outlet bracket)
Black (chassis)