



| | | |
|------------------------|------|-----|
| 63A model : | Fuse | MCB |
| VP36C13-63A-CR_EN/2B-2 | - | 6 |

- Input Rating : 63A, 400V
- Inlet : 63A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 10.0mm sq. H07RN-F cordset
- Protection : 30A single pole hydraulic MCB x 6
- Bank Details :
 - PH-1** < **Bank 1** > Output 30A max. C 13 # 1-11 (odd)
 - < **Bank 2** > Output 30A max. C 13 # 2-12 (even)
 - PH-2** < **Bank 3** > Output 30A max. C 13 # 1-11 (odd)
 - < **Bank 4** > Output 30A max. C 13 # 2-12 (even)
 - PH-3** < **Bank 5** > Output 30A max. C 13 # 1-11 (odd)
 - < **Bank 6** > Output 30A max. C 13 # 2-12 (even)

Three phase basic PDU
Outlet : 10A Rated IEC320 C13 x 36



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
Copyright 2015 Synergy Global Technology Inc. All rights reserved.

| | | |
|------------------------|---|---|
| EMC Compliance | : | FCC & CE certified |
| Safety Compliance | : | CE / LVD certified |
| Environment Compliance | : | RoHS2 & REACH |
| Operating Temperature | : | -5 to 60 °C |
| Storage Temperature | : | -25 to 65 °C |
| Operating Altitude | : | 0 to 2,000 m |
| Storage Altitude | : | 0 to 15,000 m |
| Humidity | : | 8 to 95% RH, non-condensing |
| Dimension | : | 100 (W) x 70 (D) x 1550 (H) mm |
| Material | : | Steel |
| Color | : | White (outlet bracket) Black (chassis) |