



63A model :	Fuse	MCB
VP48C13-63A-CR_EN/2B-2	-	6

- Input Rating : 63A, 400V  
 Inlet : 63A IEC60309 3P+N+E 6hr Red plug  
 Cordset : 5-wire 2 meter 10.0mm sq. H07RN-F cordset  
 Protection : 30A single pole hydraulic MCB x 6  
 Bank Details : **PH-1** < **Bank 1** > Output 30A max. C 13 # 1-15 (odd)  
                   < **Bank 2** > Output 30A max. C 13 # 2-16 (even)  
**PH-2** < **Bank 3** > Output 30A max. C 13 # 1-15 (odd)  
                   < **Bank 4** > Output 30A max. C 13 # 2-16 (even)  
**PH-3** < **Bank 5** > Output 30A max. C 13 # 1-15 (odd)  
                   < **Bank 6** > Output 30A max. C 13 # 2-16 (even)

**Three phase basic PDU**  
 Outlet : 10A Rated IEC320 C13 x 48



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.  
 Copyright 2015 Synergy Global Technology Inc. All rights reserved.

EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

Dimension : 100 (W) x 70 (D) x 1775 (H) mm  
 Material : Steel  
 Color : White ( outlet bracket )  
           Black ( chassis )