

# LCDR5U10-03 10.4" LCD RACKMOUNT MONITOR WITH 24W SPEAKERS



- Dual 10.4" TFT LCD display (1024 x 768 resolution) in only 5U (8.75") of rack space.
- ARGB (Analog RGB) and DVI-D signal inputs (optional S-Video/Composite Video inputs).
- Housed in rugged steel construction with a black powder coat finish.
- Integrated 24 Watt stereo speaker with front panel controls.
- Optional Lexan. screen protection available (L).



Optional S-Video & Composite video input + ARGB

Made in U.S.A.



## GENERAL SPECIFICATIONS

### Dimensions:

19.0" (W) x 8.75" (H) x 5" (D)

### Weight:

11 lbs

### Power:

100 - 240 VAC, 50/60 Hz.  
60 Watts max.

### On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical  
Position, Auto Adjust, OSD H & V Position, Input Select  
Color Temp., Reset.

### Plug & Play:

DDC1 and DDC2B

### Temperature:

Operating: 0°C to 50°C  
Storage: -20°C to 60°C

### Humidity:

Operating: 10 to 90% RH (max)

### Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

### Input Signal (Digital):

DVI-D (TDMS).

### Input Connectors:

Analog: 15-pin mini D-Sub.  
Digital: 24 pin DVI-D.

### Colors Available:

Black.

## DISPLAY SPECIFICATIONS

### Display Type:

Active matrix TFT LCD

### Viewable Size:

10.4" Diagonal.

### Colors Displayed:

262k colors.

### Contrast Ratio:

500:1

### Brightness:

350 cd/m<sup>2</sup> typ.

### Viewing Angle (CR>5):

Horizontal: 178°  
Vertical: 178°

### Response Time:

40ms Typ.

### Resolution:

VGA up to 1024 x 768.

### Horizontal Frequency:

30 to 81 KHz.

### Vertical Frequency

55 to 75 Hz.

### Screen Protection:

Lexan. optional.

## SPEAKER SPECIFICATIONS

### Front Panel Controls:

Power ON/OFF switch, Volume control,  
Headphone jack, Power Indicator.

### Audio Output:

24 Watts

### Audio Input Connector:

3.5mm Stereo jack.

Supplied with VGA cables, AC/DC adapter and power cord.

Contact us about other options and our additional rack mount products.