



*** Example only. Components are optional

Specifications

- **EIA RS-310C 19" Rackmount Standard**
- **Construction:** Heavy Duty Cold Rolled Electroplated Steel
- **Color:** Black (Standard), Beige or Custom
- **Support Dual Mini-ITX M/B (Max. to 6.7" x 6.7")**
- **Drive Capacity :** 2x 3.5"HDD
- **Power Supply(Optional):** 1U Single 200W ATX P/S Max. Depth 150mm
- **Cooling:** 3x (40mm = 15.3CFM ea.) Fans
- **Connector Port (Front):** 4x USB Ports
- **Indicators:** LEDs for Power ON/OFF, HDD Activity
- **Switch:** Power ON/OFF, System Reset
- **Dimensions (W x H x D):** 483 x 44 x 400mm (19" x 1.7" x 15.8")
- **Cuft:** 2.1
- **GW:** 7.6 kgs / 16.8 lbs
- **Carton Size(cm):** 58 x 18.5 x 55.5 (22.8" x 7.3" x 21.9")
- **Humidity :** 5% - 95% Non-condensing

Dimension

