



### Key Features

- Up to 16 TB of disk capacity & higher
- Two ports MiniSAS 8088 connectors
- Eight hot-swappable disk module, 3.5" SATA II drives each with up to 32MB cache & higher
- Low noise cooling fan ensures data integrity
- Universal power supply: 120-240VAC universal auto switching
- Unique design, aluminum enclosure finished
- Mac OS X , Windows® & Linux compatible
- Standard 1-Year factory warranty

### Kit Contents

- 8 Bay MiniSAS Rackmount Enclosure
- A/C Cable
- Accessories Box
- User Guide (Available download online)
- 8 X removable drive modules



### Qualified RAID Controller Cards



- Areca - 1221X PCI-E (SATA)
- Areca - 1680X PCI-E (SAS/SATA)
- ATTO - R380 PCI-E (SAS/SATA)
- HighPoint - 2322 PCI-E (SATA)
- HighPoint - 4322 PCI-E (SAS/SATA)



- Areca - 1221X PCI-E (SATA)
- Areca - 1680X PCI-E (SAS/SATA)
- ATTO - R380 PCI-E (SAS/SATA)
- HighPoint 4322 PCI-E (SAS/SATA)

### Optional - Not Included

- (1) PCI-E HBA RAID Controllers
  - PCI-Express RAID Controller



- (1) MiniSAS 8088 Cable
  - 2 X MiniSAS 8088 Cable (1 Meter)



Model	Capacity	Enclosure Type	Array Type	Number of Disks	Disk Interface
SS2007	Up to 16TB (8 X 2TB)	Rackmount Array	JBOD PCI RAID Card Required (Optional)	8 Removable	SATA II & SAS
	Host Interface	Fan Cooling	Supported OS	PSU	Dimension (LxWxH)
	Two MiniSAS 8088	Low Noise Fan	Mac OS X Windows Linux	Universal Auto-switching	19" X 3.5" X 21.5"