



### Key Features

- Up to 16 TB of for each SAS Expander Box
- Three ports MiniSAS 8088 connectors ( 1 host , 2 Expansions)
- SAS Expansion ready, daisy chain multiple systems
- Eight hot-swap 3.5" SAS/SATA II drivedisk modules
- Low noise cooling fan ensures data integrity
- Universal power supply: 120-240VAC Universal auto switching
- Unique design, aluminum enclosure finished
- Mac OS X , Windows® & Linux compatible

### Kit Contents

- 8 Bay Rackmount Enclosure
- A/C Cable
- Accessories Box
- User Guide
- 8 X removable drive modules
- 1 X MiniSAS 8088 Cable (1 Meter)



### Qualified RAID Controller Cards



- Areca – 1680X PCI-e (SATA/SAS)
- Areca – 1680IX PCI-e (SATA/SAS)
- ATTO - R380 PCI-e (SAS/SATA)
- Highpoint - 4322 PCI-e (SAS/SATA)



- ATTO - R380 PCI-e (SAS/SATA)
- Areca – 1680X PCI-e (SATA/SAS)
- Areca – 1680IX PCI-e (SATA/SAS)
- Highpoint - 4322 PCI-e (SAS/SATA)

### Optional - Not Included

- (1) PCI-E HBA RAID Controllers
  - PCI-Express RAID Controller



Model	Capacity	Enclosure Type	Array Type	Number of Disks	Disk Interface
SS2008	Up to 16TB (8 X 2TB)	Rackmount Array	JBOD PCI RAID Card Required (Optional)	8 Removable	SATA II & SAS
	Host Interface	Fan Cooling	Supported OS	PSU	Dimension (LxWxH)
	3 x MiniSAS 8088 1 x Host 2 x Expander	Low Noise Fan	Mac OS X Windows Linux	Universal Auto-switching	19" X 3.5" X 21.5"