



1920 x 1200
Ultra High Resolution




Drawer Features & Display Benefits

- ▶ 1U 17" widescreen LCD drawer with DVI-D / VGA input
- ▶ 1920 x 1200 native **WUXGA** Ultra high resolution
- ▶ Support **Full HD** with 1080p resolution
- ▶ Green LED-backlit panel technology
- ▶ 8-bit colors
- ▶ Enhanced aesthetics with molded front panel and two point lock
- ▶ Short depth design of 460mm (18.1") only

Options

- 3G / HD / SD-SDI Broadcast-grade input
- 17" Touchscreen : Capacitive, Resistive
- HDMI or Audio input
- 48V, 24V or 12VDC input



Standard I/O : VGA and DVI-D

Options I/O : HDMI, Audio
SDI, USB for touchscreen

Specifications

• LCD Panel

Size (diagonal) : 17.1" widescreen TFT
 Max resolution : 1920 x 1200
 Brightness (cd/m2) : 210
 Backlight : LED
 Colors : 16.7 M, 8-bit
 Contrast ratio (typ) : 600 : 1
 Viewing angle (H/V) : 130° x 110°
 Active area (mm) : 367 x 230
 MTBF (hrs) : 20,000
 Signal input : VGA or DVI-D

• Casing Color : Black (RAL 9005)

• Weight

Net : 11 kgs
(24 lbs)

• Environmental

Operating : 0 to 50°C Degree
 Storage : -5 to 60°C Degree
 Relative humidity : 5~90%, non-condensing
 Shock : 10G acceleration (11 ms duration)
 Vibration : 5~500Hz 1G RMS random vibration

• Regulatory : FCC, CE

• Power

Input : Auto-sensing 100 to 240VAC, 50 / 60Hz
 Consumption : Max. 48 Watt, Standby 5 Watt

• Dimensions

Product : 441.6 x 460 x 44 mm / 17.4 x 18.1 x 1.73 inch

Diagrams (mm)

