



Ultra short depth
480mm / 18.9" only



Benefits

- ▶ 1U 17" LCD console drawer
- ▶ Dual slide - LCD and keyboard slide independently
- ▶ Ultra short depth 480mm / 18.9"
- ▶ 1920 x 1080 native resolution / 16.7M colors (8-bit)
- ▶ HDMI 1.4 + DP 1.2 + VGA video input / USB KB / MS
- ▶ Dual stereo speakers for HDMI 1.4 & DP 1.2
- ▶ Ideal for open rack / short depth rack
- ▶ 104-key keyboard with touchpad
- ▶ One Man installation design
- ▶ Enhanced aesthetics with new molded front panel and 2-point lock

Options

- 3G / HD / SD-SDI Broadcast-grade input (SDI)
- DC power : 12V / 24V / 48V / 110V / 125V / 250V
- SUN Micro keyboard available
- KVM integration

Product Specifications

Console Port	
Video input	HDMI 1.4 + DP 1.2 + VGA
KB / MS	USB interface
Console cable bundled	HDMI 1.4 cable x 1 + USB type A cable x 2

LCD Panel	
Panel size (diagonal)	17.3"
Native resolution	1920 x 1080
Brightness (cd/m ²)	300
Contrast ratio (typ.)	1000 : 1
Colors	16.7 M, 8-bit
Viewing angle (L/R/U/D)	85/85/85/85
Response time (ms)	25
Dot pitch (mm)	0.1989
Display area (mm)	381.888H x 214.812V
Surface treatment	Anti-glare, Hard-coating
Surface hardness	3H
Backlight type	LED
MTBF (hrs)	15,000

Physical	
Product (W x D x H)	442 x 480 x 44 mm / 17.4 x 18.9 x 1.73 inch
Net weight	10.6 kg / 23.4 lb

* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Mounting Distance	
Single console drawer	490 ~ 720 mm / 19.3 ~ 28.3 inch


Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption (console / KVM)	Screen on	Max. 14W / Max. 45W
	Power saving mode	Max. 2W / Max. 34W
	Power button off	Max. 1W / Nil

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	10-90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Compliance	
EMC	FCC & CE
Safety	CE / LVD & UKCA
Environment	REACH & RoHS3 / WEEE

Standard Keyboard

N keyboard with touchpad



Keyboard Options

* US layout only

Sn

SUN keyboard with touchpad



Supporting layouts

America	U.S.
EMEA	U.K.
	Germany
	France
	Russia
	Spain
Asia	Japan
	Korea