


ID-22Aw 22" Widescreen Panel Mount LCD Panel

Dimension Drawings (mm)



Applications

- Industrial process control
- Point of sales / Kiosk
- Security / Surveillance
- Flight information display


Options

- Touchscreen
- S-Video, RCA & BNC input
- DVI input
- DC power input (12 / 24 / 48 VDC)
- Audio input with speaker
- TV tuner with remote controller
- NEMA4 / IP65 2mm Protective Glass

Design features

- 6mm aluminum front bezel with 45 degree chamfer
- OSD control keys to optimize the display
- Wide 22inch 16:10 TFT LCD panel support 1680 x 1050 pixels
- 300 cd/m2 industrial brightness
- A wide range of mounting kits

Specifications

LCD Panel	
Panel Grading	Grade A TFT LCD panel
Panel Size (in.)	Wide 22" (16 : 10)
Max. Resolution	1680 x 1050
Color Support	16.7M
Brightness-nits (cd/m ²)	300 cd/m2 (Typical)
Contrast Ratio	1000 : 1 (Typical)
Pixel Pitch (mm)	0.282 x 0.282
Tr Response Time	3.6 ms
Viewing Angle (L/R/U/D)	80 / 80 / 80 / 80
OSD Control	Brightness, Contrast, Phase & Clock, Color, H & V position, Auto-tune & Recall
Connector(s)	D-Sub 15 pin VGA analog
LCD Panel MTBF (hrs)	50,000
Power	100~240VAC, 50 / 60Hz via AC adapter
Dimensions (mm)	574 x 62 x 380 (W x D x H)

Operating Temperature	0° to 50° C
Storage Temperature	-5° to 60° C
Humidity	5~90%, non-condensing
Shock	10G peak acceleration (11ms duration)
Vibration	5-500Hz, 1G RMS random vibration

Ordering information

Model no.	Description
ID-22Aw	Wide 22" panel mount LCD panel with VGA input
ID-22Aw-AV	Wide 22" panel mount LCD panel with VGA, S-Video & RCA input
ID-22Aw-BNC	Wide 22" panel mount LCD panel with VGA, S-Video & BNC input
ID-22Aw-DVI -IP65	Wide 22" panel mount LCD panel with VGA & DVI input Add NEMA4 / IP65 Protective Glass