




### 1U 15" or 17" TFT LCD Display with Keyboard and Mouse Area



Don't like touchpads or trackballs?

In addition to a choice of a high quality 15" or 17" TFT LCD display and full function compact keyboard, this unit contains a storage and use area for your favorite mouse, all housed in a convenient 1U form factor.

Some of the features are:

- Smooth action ball bearing rack mount slides.
- Display surface protected by a clear shatterproof cover.
- Display automatically powers off when in the closed position.
- Wide 160 degree horizontal and vertical viewing angles.
- 250 nits brightness and 1000:1 contrast ratio typical.
- Display resolution - 1024 x 768 (15" TFT) 1280 X 1024 (17" TFT)
- Rugged "built to last" industrial construction, **Made in USA.**
- Dimensions: 15" TFT LCD - 19.0" (W) x 1.75" (H) x 23" (D).  
17" SAMSUNG Grade A TFT LCD - 19.0" (W) x 1.75" (H) x 25.2" (D).