



Synergy Global Inc

www. RackmountMart.com

Toll Free : 1-888-865-6888

Tel : 510-226-8368 Fax : 510-226-8968

Email : sales@RackmountMart.com

LCD1U-15/17-14 Product Specification

Specification:

Size:	1U 19" Rackmount Type	
Keyboard:	Notebook type , 88 Keys	
Mouse:	Touchpad	
Dimension:	442.4 x 44 x 508 mm (WxHxD)	
Weight:	Single port: 11 kgs (28lb)	8/16 ports: 11.5 kgs (29.2lb)
Power Supply:	100/220V auto-switching, 50W	
Protection:	Front panel with Thumb screw	
	Rail with self-locking device	
	LCD back-light will be turned-off when the screen set is turned down	
Operating Temperature:	0-50°C (32-122°F)	
KVM switch	Build-in 8 or 16 ports KVM switch	

Display:

Diagonal Size:	15"(16:9)	17"(16:9)
Resolution:	1024 x 768	1280 x 768
Contrast Ratio:	350:1	600:1
Brightness:	250 nits	450 nits
Frequency:	60Hz	60Hz
Color: Native	16.2M colors	16.2M colors
Control:	OSD	OSD

Accessories:

	Single Port	8 Ports	16 Ports
KVM Drawer Unit	X 1	x 1	x 1
Extension Bracket	X 2	x 2	x 2
Power Cord	X 1	x 1	x 1
VGA HDDB 15pin (shared with PS2 keyboard and Mouse)	X 1	x 8	x 16
Screws package	X 1	x 1	x 1
External power adaptor	X 1	X 1	X 1
User Manual	X 1	x 1	x 1

