

LCD1U17-18 Sun Micro 1U RACKMOUNT Monitor With Keyboard



- Sun Micro systems compatible
- Meets EIA310c & IEC-3 specifications
- One set built-in Keyboard, touch pad & monitor
- With high brightness TFT LCD Panel
- 116-Key Keyboard with 3 buttons touchpad
- Built-in Rail self-locking device
- D-Sub 15pin to VGA, USB keyboard/Mouse Cable



Specification:

Model NO.	LCD1U17-18	LCD1U17-18-8KVM	LCD1U17-18-16KVM
Ports Switch	D-Sub 15, Single port	D-Sub 15, 8 ports	D-Sub 15, 16 ports
Dimension	1.75 x 17.42 x 23.63 inches (H x W x D)		
Power Supply	50W, AC 110/220V Auto Switch or DC+48V		
Keyboard	117-Key Keyboard with 3 buttons touchpad		
Protection	Tempered glass protection to the LCD screen		
Operation Temp	0°C -50° C (32°F -122° F)		
Relative Humidity	20-80% (non-condensing)		
Approval	CE, FCC, UL		
Display Info			
Diagonal	17"	17"	17"
LCD Resolution	1280 x 1024	1280 x 1024	1280 x 1024
Brightness	300 nits	300 nits	300 nits
Contrast	500:1	500:1	500:1
Color	16.7M colors	16.7M colors	16.7M colors
Viewing Angle	160/160	160/160	160/160
Backlight MTBF	50,000 hours under 25 +/- ° C		
Frame Rate	60Hz		