

Specification of New LCD1U19-06 :

Model No	LCD1U19-06
Ports switch for PC	None
Weight	16kgs
Dimension	442.4x44.5x650mm
Power Supply	DC +48V or AC 110/220V auto switching
Extension Cable	1x1.8 meter (standard VGA, keyboard, mouse cable)
Construction Material	Industrial Metal
Keyboard	Membrane 105 key with touchpad
Language	US (Standard), RU, IT, FR, GR, UK, CH.....
Color	Black
Protection	Tempered glass protection to the LCD screen
Security Lock	Thumb screw x 2
Operation Temperature	0-50° C (32-122°F)
Approval	CE, FCC

Display

Diagonal	19"
LCD Resolution	SXGA 1280 x 1024
Display Colors	16.2M
Brightness	300 nits
Bezel Opening Area	380.2(H) x 305(V)
Viewing angle	160/160
Contrast Ratio	450:1
Frame Rate	60Hz
Backlight	4 x CCFL units

