

New




S-Video + BNC



Touchscreen - USB




DVI-D




Touchscreen - Serial



DC Power



Audio



Options



BNC + S-Video



DVI-D



DC Power



Touch Screen



Audio



Quad Display

Drawer Features & Options

- 1U rackmount LCD drawer with 20" LCD
- Quad display option
- Touchscreen option
- 12V, 24V and 48V DC Power options
- AV + BNC, Audio and DVI-D options

LCD Drawer Benefits

- ▶ 20" LCD in 1U with 1600 x 1200 high resolution
- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed
- ▶ Enhanced aesthetics with new molded front panel and two point lock

Monitor  Grade A 20" industrial TFT LCD panel

- 20" 1600 x 1200 LCD with 300 nit brightness and 800:1 contrast ratio typical

Ordering Information

Model	LCD1U20-011
-------	-------------

Dimensions

Model	Product Dimension (W x D x H)	Net Weight
LCD1U20-011	442 x 650 x 44 mm 17.4 x 25.6 x 1.73 inch	14 kg / 31 lbs

Diagram

Unit : mm

