

LCDK1024/1025 1U Rackmount 2 Console PS2 DB-15 8/16 port KVM switch



Designed for:



Two Console KVM Benefits

- ▶ 8 or 16 ports in 1U of rack space
- ▶ Secure remote (Two) console over 300M of Cat5 cable
- ▶ Cost efficient remote server management between user and equipment rooms within the building

Technical Specification

- KVM Port**
 - Number of ports : 8 or 16
 - Connector : HDDB 15-pin
 - Connectivity : 3-in-1 KVM cable in 6, 10 & 15 & 33 feet
- Console**
 - Graphic connector : HDDB 15-pin, VGA
 - Resolution : Up to 1920 x 1440
 - Input device : 2 x USB type A for keyboard & mouse
- On Screen Display**
 - Port name : Up to 10 characters long
 - Port select : Front membrane button, Hotkey & On screen menu
 - Security : Support eight character password
 - Auto scan : 5~99 seconds
- Expansion :** Up to 128 servers by 8-level cascade
- Compatibility**
 - Multi-platform : Mix PCs, SUNs, IBMs, HPs, DELLs Server
 - Support : Windows Vista, 2003 / XP / 2000, Linux, Netware, Unix, DOS
- Power**
 - Input : 100 or 240V AC at 50 or 60 Hz via AC adapter
 - Option DC : 12V / 24V / 48V DC input
- Regulatory Approval :** FCC, CE
- Environmental**
 - Operating : 0 to 50°C
 - Storage : -10 to 60°C
 - Relative humidity : 90%, non-condensing
 - Shock : 50G peak acceleration (11ms, half-sine wave)
 - Vibration : 58~100Hz / 0.98G (11min / cycle)

Accessories

LCD-A1004
LCD-A1005
LCD-A1006
LCD-A1007



PS/2 3-in-1 KVM cable
6ft, 10ft, 15ft & 33ft available

LCD-A1019



6ft cascade cable

LCD-A1001



PS/2 to SUN / USB adapter

Dimensions

Model	Product Dimension (W x D x H)	Net Weight
LCDK1024	443 x 180 x 44 mm 17.4 x 7.1 x 1.73 inch	4 kg / 9 lbs
LCDK1025	443 x 180 x 44 mm 17.4 x 7.1 x 1.73 inch	4 kg / 9 lbs