


# LCDK1034 1U Rackmount Keyboard with 88 key and Mouse use area besides keyboard

Made in U.S.A

Front Panel Option (Standard Color is Black)



Standard



-R : w/ Retainer Screws Option



-R-L : w/ Retainer Screw + Lock Option



-L : w/ Lock option



## Features & Options

- 1 rack unit high (1.75").
- PS/2 compatible keyboard with mouse use area beside keyboard
- 8.5" deep storage area behind keyboard
- Choice of front panel options (lock, retainer, blank).
- Optional USB connector and Mouse.
- Slides lock in the extended position to provide stability.
- Ball bearing slides with mounting length adjustable from 23" to 30".

## GENERAL SPECIFICATIONS

### Depth

20"

### KVM use:

N/A

### Interface:

PS2 OR USB

### Options:

Lock , Retainers

### Dimension:

20.25" x 17.75" x 1.75" (LxWxH)

### Standard Paint Color:

Black or White

### Keyboard:

88 key PS/2 compatible keyboard  
with mouse use are beside keyboard

## ORDERING INFORMATION

LCDK1034-bk	1U Rackmount Keyboard Drawer with 88 key PS/2 compatible keyboard with mouse use area beside keyboard , black , PS2 (mouse is not included)
LCDK1034-w	1U Rackmount Keyboard Drawer with 88 key PS/2 compatible keyboard with mouse use area beside keyboard , white, PS2 (mouse is not included)
LCDK1034-bk-u	1U Rackmount Keyboard Drawer with 88 key PS/2 compatible keyboard with mouse use area beside keyboard , black , USB (mouse is not included)
LCDK1034-w-u	1U Rackmount Keyboard Drawer with 88 key PS/2 compatible keyboard with mouse use area beside keyboard , white, USB (mouse is not included)
-R	Add retainers
-L	Add Lock
-R-L	Add retainer and Lock
-MP	Add Optical PS/2 Mouse
-MS	Add Optical USB Mouse

Specifications subject to change without notice.