

LCDK 1040 IP KVM Extender

Features

- Remotely manage servers from anywhere through Internet using a web browser
- Embedded processor for remote access and control
- BIOS level access
- Upgradeable firmware
- Automatic video resolution sensing for best possible display



Specifications

PC / Consol Port	1
PC Port Connector (All Female Types)	PS/2 Keyboard Mini Din 6 pin; PS/2 Mouse Mini Din 6 pin; VGA HDDB 15 pin; USB Type B receptacle
Consol Port Connector (All Female Types)	Local Console: PS/2 Keyboard mini Din 6 pin; VGA HDDB 15 pin; PS/2 Mouse Mini Din 6 pin; Remote Console: RJ-45 8P8C
Serial Port	1 (DB9 pin Male)
1 LAN port	(RJ-45, supporting 10/100BASE-T)
Reset Botton	Yes
Keyboard / Mouse Emulation	PS/2
VGA Resolution (Max)	Local :1600 X1200 Remote : 1280 X1024
Housing	Metal
Power Adapter	DC 5V,2.5A
Operating/Storage Temperature	Operate:0 ~ 50 C / Storage: -20 ~ 60
Humidity	0~80%,Non-Condensing
Weight	1700g
Dimension	156 x 139 x 27 (W x H x D) cm