

LCD8U19-08 19" TFT RACK MOUNT MONITOR



Synergy Global Technology Inc

www.RackmountMart.com

- Mounts in 8U of rack space.
- 19" TFT LCD display with 1280 x 1024 resolution.
- Steel front panel construction with a durable powder coat finish.
- Wide viewing angles allow mounting higher in rack.
- High contrast ratios for excellent picture quality.
- Analog and Digital inputs.



Made in U.S.A.

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 14.0" (H) x 2.7" (D)

Weight:

10.5 lbs.

Power:

100 - 240 VAC, 50/60 Hz.

38 Watts max.

On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical Position, Auto Adjust, OSD H & V Position, Input Select Color Temp., Reset.

Plug & Play:

DDC1 and DDC2B

Temperature:

Operating: 10°C to 40°C

Storage: -20°C to 45°C

Humidity:

Operating: 10 to 80% RH (max)

Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

Input Signal (Digital):

DVI-D (TMDS).

Input Connectors:

Analog: 15-pin mini D-Sub.

Digital: 24 pin DVI-D.

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

Active matrix TFT LCD

Display area:

19" Diagonal.

Colors Displayed:

16.2 million colors.

Contrast Ratio:

700:1

Brightness:

300 cd/m² typ.

Viewing Angle:

Horizontal: 160°

Vertical: 160°

Response Time:

8ms

Resolution:

VGA up to 1280 x 1024.

Horizontal Frequency:

30 to 81 KHz.

Vertical Frequency:

56 to 75 Hz.

Specifications subject to change without notice.

Contact us about other options and our additional rack mount products.

www.rackmountmart.com
email : sales@rackmountmart.com

SYNERGY GLOBAL TECHNOLOGY INC 1-888-865-6888