

# 19" LCD RACK MOUNT MONITOR



- Mounts in 8U of 19" rack space.
- 19" TFT LCD display with 1280 x 1024 resolution.
- Steel front panel construction with a durable powder coat finish.
- High contrast ratios for excellent picture quality.
- Analog and Digital inputs.

## GENERAL SPECIFICATIONS

### Dimensions:

19.0" (W) x 14.0" (H) x 2.7" (D)

### Weight:

10.5 lbs.

### Power:

100 - 240 VAC, 50/60 Hz.  
38 Watts max.

### On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical  
Position, Auto Adjust, OSD H & V Position, Input Select  
Color Temp., Reset.

### Plug & Play:

DDC1 and DDC2B

### Temperature:

Operating: 10°C to 40°C  
Storage: -20°C to 45°C

### Humidity:

Operating: 10 to 80% RH (max)

### Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

### Input Signal (Digital):

DVI-D (TMDS).

### Input Connectors:

Analog: 15-pin mini D-Sub.  
Digital: 24 pin DVI-D.

### Colors Available:

Black.

## DISPLAY SPECIFICATIONS

### Display Type:

Active matrix TFT LCD

### Display area:

19" Diagonal.

### Colors Displayed:

16.2 million colors.

### Contrast Ratio:

8000:1 Dynamic

### Brightness:

250 cd/m<sup>2</sup> typ.

### Viewing Angle (CR>10):

Horizontal: 170°  
Vertical: 160°

### Response Time:

5ms

### Resolution:

VGA up to 1280 x 1024.

### Horizontal Frequency:

30 to 81 KHz.

### Vertical Frequency:

56 to 75 Hz.

Specifications subject to change without notice.

## MODEL NUMBER

LCDR8U19-10

LCDR8U19-10-L (with Lexan™ screen protection)

**Made in U.S.A**

*Contact us about other options and our additional rack mount products.*