

21" TFT RACK MOUNT MONITOR FOR 24" WIDE RACKS



S-video, Composite and Audio Inputs



Power, DVI, VGA, Audio and Component inputs



- Mounts in 8U of rack space with mounting brackets to accommodate 24" rack width.
- 21" Wide format TFT LCD display with 1680 x 1050 resolution.
- Steel front panel construction with a durable powder coat finish.
- Wide viewing angles and high contrast allow versatile mounting choices.
- Picture-In-Picture, Picture-By-Picture and built-in internal speakers.
- Optional Lexan™ screen protection available.

GENERAL SPECIFICATIONS

Dimensions:

24.0" (W) x 14.0" (H) x 2.8" (D)

Weight:

17.5 lbs.

Power:

100 - 240 VAC, 50/60 Hz.
75 Watts max.

Plug & Play:

DDC1 and DDC2B

Temperature:

Operating: 10°C to 40°C
Storage: -20°C to 45°C

Humidity:

Operating: 10 to 80% RH (max)

Input Video Signals:

R.G.B. analog, DVI Digital Link: TDMS, Composite, S-video, Component.

Sync Type:

Separate H/V Composite H/V SOG.

Input Connectors:

15 pin D-sub, DVI-D, CVBS, S-video, Component.

Compatibility:

PC/Windows, Macintosh, Sun Microsystems

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

a-si LCD TV/monitor

Viewable Size:

21" wide format.

Colors Displayed:

16.7 million colors.

Contrast Ratio:

1000:1

Brightness:

300 cd/m² typ.

Viewing Angle:

Horizontal: 178°
Vertical: 178°

Response Time:

8 ms (G to G)

Native Resolution:

1680 x 1050.

Horizontal Frequency:

30 to 81 KHz.

Vertical Frequency:

56 to 75 Hz.

Specifications subject to change without notice.

Contact us about other options and our additional rack mount products.



www.RackmountMart.com

Tel: 510-226-8368

Fax: 510-226-8968



620 Berryessa Road



SYNERGY GLOBAL, INC.

1-888-865-6888