

LCDR8U22-04 22" Widescreen Rackmount LCD Display for 24" Racks

New



Made in U.S.A.

- Mounts in 8U of vertical rack space in a 24" rack width.
- 22" Wide format TFT LCD display with 1680 x 1050 resolution.
- Fast video response time provides sharp text and crisp motion.
- 16:10 aspect ratio features a widescreen viewing area.
- Steel front panel construction with a durable paint finish.
- Optional Lexan™ screen protection available.

GENERAL SPECIFICATIONS

Dimensions:

24.0" (W) x 14.0" (H) x 2.8" (D)

Weight:

16.5 lbs.

Power:

100 - 240 VAC, 50/60 Hz.

55 Watts max.

Plug & Play:

DDC2B

Temperature:

Operating: 10°C to 40°C

Storage: -20°C to 45°C

Humidity:

Operating: 10 to 80% RH (max)

Input Video Signals:

R.G.B. analog, DVI Digital Link: TDMS.

Sync Type:

Separate H/V, Composite H/V, SOG.

Input Connectors:

15 pin D-sub, DVI-D.

Compatibility:

PC/Windows, Macintosh.

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

a-si TFT/TN

Viewable Size:

22" wide format.

Colors Displayed:

16.7 million colors.

Contrast Ratio:

700:1

Brightness:

280 cd/m² typ.

Viewing Angle (CR>5):

Horizontal: 160°

Vertical: 160°

Response Time:

5 ms (G to G)

Native Resolution:

WSXGA+ (1680 x 1050).

Pixel Pitch:

.282 mm.

Specifications subject to change without notice.