

LCDR8U23-01 23" 16:9 Full HD Monitor



- Mounts in 8U of rack space with mounting brackets to fit 19" rack width.
- 23.0" 16:9 format TFT LCD display with full HD 1920 x 1080 resolution.
- Fast video response time provides sharp text and crisp motion.
- IPS LCD panel provides wide viewing angles (U/D, L/R).
- 1000:1 Static contrast ratio for superior detail.
- Optional Lexan™ screen protection available.

GENERAL SPECIFICATIONS

Dimensions:
22.75" (W) x 14.0" (H) x 3.0" (D)

Weight:
17.0 lbs.

Power:
100 - 240 VAC, 50/60 Hz.
45 Watts typ.

Plug & Play:
DDC2B

Temperature:
Operating: 0°C to 40°C

Humidity:
Operating: 20 to 90% RH (max)

Input Video Signals:
R.G.B. analog, DVI (with HDCP)

Input Frequency:
Fh: 22-82 KHz, Fv: 50-75 Hz.

Sync Type:
Separate H/V, Composite H/V, SOG.

Input Connectors:
15 pin D-sub, DVI-D.

Compatibility:
PC/Windows, Macintosh.

Colors Available:
Black.

DISPLAY SPECIFICATIONS

Display Type:
TFT active matrix with IPS LCD.

Viewable Size:
23.0" diagonal.

Colors Displayed:
16.7 million colors.

Contrast Ratio :
1000:1.

Brightness:
300 cd/m² typ.

Viewing Angles:
178°/178° H/V.

Response Time:
14 ms Typ.

Optimum Resolution
1920 x 1080.

Light Source:
Long Life (50,000 hrs typ).

Panel Surface:
Anti-glare.



Contact us about other options and our additional rack mount products.