

LCDR5U10-05-dual DUAL 10.4" RACK MOUNT MONITOR



Features & Options

- Dual 10.4" TFT LCD display (1024 x 768 resolution) in 5U (8.75") of rack space.
- Both monitors feature ARGB (Analog RGB) and speak.
- Housed in rugged steel construction with a black powder coat finish.
- Supplied with VGA cables, AC/DC adapter and power cord.
- Available composite video inputs via BNC and S-Video connector .



GENERAL SPECIFICATIONS

Dimensions:

19.75" (W) x 8.72" (H) x 2.33" (D)
(2.33" (D) out of front rack posts).

Power:

110 - 240 VAC, 50/60 Hz.
60 Watts max.

On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical
Position, Auto Adjust, OSD H & V Position, Input Select
Color Temp., Reset.

Plug & Play:

DDC1 and DDC2B

Temperature:

Operating: 0°C to 50°C
Storage: -5 °C to 60°C

Humidity:

Operating: 10 to 90% RH (max)

Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

Input Signal (Digital) Option:

DVI-D (Option).

Input Signal (Composite) Option:

BNC and S-Video inputs available.

Input Connectors:

Analog: 15-pin mini D-Sub. Audio

Colors Available:

Black.

Specifications subject to change without notice.

DISPLAY SPECIFICATIONS (APPLY TO EACH DISPLAY)

Display Type:

Active matrix TFT LCD

Display area:

10.4" Diagonal.

Colors Displayed:

16.2M colors.

Contrast Ratio:

1200:1 typ.

Brightness:

400 cd/m² typ.

Viewing Angle:

Horizontal: 176°

Vertical: 176°

Response Time:

25ms Typ.

Resolution:

VGA up to 1024 x 768.

Horizontal Frequency:

31.5 to 80KHz.

Vertical Frequency:

56 to 75 Hz.

We offer OEM and custom solutions.
Contact us for additional information.