

# RA5003-8



Front



Rear



P/N	RA5003-8		
Rating	125VAC/15A (UL Derated 12A) 1440W		
Receptacle	Type	NEMA 5-15R with Grounding Contact	
	Quantity	Front	Rear
		0	8
Case	SPCC with Black painting		
Switch	Single Pole Switch with Protective Cover		
Over Current Protector	15A Circuit Breaker		
Ampere Meter	None		
Surge Protection	A2 Level with LED		
Plug	NEMA 5-15P		
Power Cord	SJT 14/3C 60°C , 15ft		
Size	482.6mm x 88.9mm x 44.2mm , 1U Size Apply To Rack Mount		

