

RK 1005



White Front Panel



Rear View - 110VAC Power Supply



Rear View - 110/220VAC Power Supply

2U Rack Mount 24 Watt Speaker

Fully enclosed amplified stereo speaker system with front panel controls which include a Power ON/OFF Switch with Power Indicator and separate Volume Control. A front panel Headphone Jack disables the internal speakers when a headphone plug is inserted, directing audio output to the headphones. The unit is supplied with a detachable audio cable and an external 110 VAC 60 Hz input power supply (optional 110/220 VAC 50/60 Hz input power supply).

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 3.5" (H) x 3.5" (D)

Weight:

4.7 lbs

Power Supply:

Standard - 110 VAC, 60 Hz.

Optional - 110/220 VAC, 50/60 Hz.

Colors Available:

Black (B) and White (W).

Front Panel Controls:

Power ON/OFF switch, Volume Control, Headphone Jack, Power Indicator.

Audio Amplifier Output:

24 Watts.

Audio Input Connector:

1/8" (3.5mm) stereo jack.

Specifications subject to change without notice.

