




Synergy Global Technology Inc

www.RackmountMart.com

Switched Rack PDU

AS-108-515-15A-515



No.	Item	Description/Function
1	Outlets	<p>The outlets connect the PDU to equipment in your rack or enclosure. Each outlet allows independent control of the connected equipment, and provides 24 independent Outlet User accounts.</p> <p>Each PDU has eight outlets: AS-108-515-15A-515 : NEMA 5-15R (shown) AS-108-520-20A-L520 : NEMA 5-20R</p>
2	Power Cord	<p>The power cord connects the PDU to one power source. The cord is located on the front of the PDU for easier mounting and user access.</p> <p>The 12-foot cord has one of the following plugs: AS-108-515-15A-515 : NEMA 5-15P (shown) AS-108-520-20A-L520 : NEMA L5-20P</p>

Specifications

AS-108-515-15A-515
AS-108-520-20A-L520

	AS-108-515-15A-515	AS-108-520-20A-L520
Electrical		
Input connectors	100–120 VAC, 12 A NEMA 5-15P plug	100–120 VAC, 16 A NEMA L5-20P plug
Output connectors	Eight NEMA 5-15R outlets	Eight NEMA 5-20R outlets
Physical		
Size (h × w × d)	1.73 × 17.50 × 4.25 in (4.45 × 44.45 × 10.80 cm)	
Weight	5 lb (2.26 kg)	
Environmental		
Elevation (above MSL):		
Operating:	0 to 10,000 ft (0 to 3000 m)	
Storage:	0 to 50,000 ft (0 to 15 000 m)	
Temperature:		
Operating:	23 to 113° F (–5 to 45° C)	
Storage:	–13 to 149° F (–25 to 65° C)	
Humidity:		
Operating:	5 to 95%, non-condensing	
Storage:	5 to 95%, non-condensing	
Approvals		
EMC Verification	FCC Part 15 Class A, ICES-003 Class A, VCCI Class A	
Safety Verification	UL/cUL Listed to UL 60950	UL/cUL Listed to UL 60950