



Key Benefits

- ▶ Screen Size:7 inches
- ▶ Resolution:1920x1200
- ▶ Aspect Ratio:16:10
- ▶ Housing Material:Metal
- ▶ Brightness:1000 nits
- ▶ Inputs:HDMI 2.0, 12G-SDI, Tally, LAN
- ▶ Professional-use durability & around-the-clock operation



DISPLAY	Panel	2x7" LTPS
	Physical Resolution	1920x1200
	Aspect Ratio	16:10
	Brightness	1000 nits
	Contrast	1200:1
	Viewing Angle	160°/ 160°(H/V)
	HDR Supported	HLG; ST2084 300/1000/10000
INPUT	HDMI	2 (HDMI 2.0)
	12G-SDI	2
OUTPUT	HDMI	2 (HDMI 2.0)
	12G-SDI	2
SUPPORTED FORMATS	HDMI	2160p 24/25/30/50/60, 1080p 24/25/30/50/60, 1080i 50/60, 720p 50/60.
	12G-SDI	2160p 24/25/30/50/60, 1080p 24/25/30/50/60, 1080i 50/60, 720p 50/60.
AUDIO IN/OUT	Speaker	-
	Audio Channel	HDMI 8ch / SDI 16ch
	Ear Jack	3.5mm - 2ch 48kHz 24-bit
POWER	Input Voltage	DC 12-24V
	Power Consumption	<21W (12V)
ENVIRONMENT	Operating Temperature	0°C-50°C
	Storage Temperature	-20°C-60°C
DIMENSION	Dimension(LWD)	480mm x 131.6mm x 32.5mm
	Weight	1.83kg