



- Mounts in 8U of rack space with mounting brackets to fit 19" rack width.
- 23" Wide format TFT LCD display with full HD 1920 x 1080 resolution.
- LED backlight and super wide 178/178 degree viewing angles.
- 1080p 16:9 aspect ratio provides a widescreen viewing area.
- 50,000,000:1 contrast ratio for superior detail.
- Energy Star & RoHS Compliant.

GENERAL SPECIFICATIONS

Dimensions:

22.75" (W) x 14.0" (H) x 3.0" (D)

Weight:

14 lbs.

Power:

100 - 240 VAC, 50/60 Hz.
32 Watts typ.

Plug & Play:

DDC2B

Temperature:

Operating: 0°C to 50°C
Storage: -20°C to 60°C

Humidity:

Operating: 20 to 90% RH (non-condensing)

Input Video Signals:

R.G.B. analog, DVI (with HDCP), HDMI

Input Frequency:

Fh: 30-83 KHz, Fv: 50-75 Hz.

Sync Type:

Separate H/V, Composite H/V, SOG.

Input Connectors:

HDMI, 15-pin D-sub, DVI-D.

Colors Available:

Black.



Offering OEM and custom solutions.
Contact us for additional information.

DISPLAY SPECIFICATIONS

Display Type:

TFT IPS LCD.

Viewable Size:

23.0" diagonal.

Colors Displayed:

16.7 million colors.

Contrast Ratio (Typ/Dyn):

1000:1 / 50,000,000:1

Brightness:

250 cd/m² typ.

Viewing Angles:

178°/178° H/V.

Response Time:

5 ms Typ.

Optimum Resolution

1920 x 1080 non-interlaced.

Light Source:

LED

Specifications subject to change without notice.

MODEL NUMBER

LCDR8U23-03

LCDR8U23-03-L with Lexan™ Screen Protection

