

LCDR7U19-06 19" 16:10 FORMAT MONITOR



- Mounts in 7U of 19" rack space.
- Wide format 16:10 aspect ratio.
- Fast 5 ms response time.
- 19" TFT LCD display with 1440 x 900 resolution.
- Analog (ARGB) and Digital (DVI-D) input connectors.
- Energy saving LED backlight.

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 12.25" (H) x 2.8" (D)

Power:

100 - 240 VAC, 50/60 Hz.
30 Watts.

On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical
Position, Auto Adjust, OSD H & V Position, Input Select
Color Temp., Reset.

Plug & Play:

DDC2B

Temperature:

Operating: 10°C to 40°C
Storage: -20°C to 45°C

Humidity:

Operating: 10 to 80% RH (max)

Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

Input Signal (Digital):

DVI with HDCP.

Input Connectors:

Analog: 15-pin mini D-Sub.
Digital: 24 pin DVI-D.

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

Active matrix TFT LCD

Display area:

19" Wide.

Colors Displayed:

16.7 million colors.

Contrast Ratio:

1,000:1 (5M:1 Dynamic)

Brightness:

250 cd/m² typ.

Viewing Angle:

Horizontal: 170°
Vertical: 160°

Response Time:

5 ms.

Resolution:

Up to 1440 x 900.

Aspect Ratio:

16:10.

Backlight type:

LED

Specifications subject to change without notice.

MODEL NUMBER

LCDR7U19-06

LCDR7U19-06-Lex with Lexan™ Screen Protection

*Contact us about other options and
our additional rack mount products.*

