

Basic 1U Fan Tray



RA4015-9



Benefits

- ▶ 1U rackmount w/ 3, 6 or 9 fans
- ▶ External temperature sensor x 1
- ▶ Front temperature LED
- ▶ Auto-sensing 110V to 220VAC power input
- ▶ 48V, 24V or 12VDC power option

Product Specifications

Basic Fan		RA4015-3	RA4015-6	RA4015-9
No. of Fan		3	6	9
Mounting		1U	1U	1U
Unit CFM (approx.)		324 CFM	648 CFM	972 CFM
Individual Fan CFM			108 CFM	
MTBF			50,000 hrs	
Individual Fan Noise Level			41 dB	

Physical		RA4015-3	RA4015-6	RA4015-9
Dimensions (W x D x H)	Product	480 x 298 x 44 mm	480 x 458 x 44 mm	480 x 623 x 44 mm
		18.9 x 11.7 x 1.73 inch	18.9 x 18 x 1.73 inch	18.9 x 24.5 x 1.73 inch
Weight	Net	4 kg / 8.8 lb	6.8 kg / 15 lb	9 kg / 19.8 lb
Casing Color		Black		

Power		RA4015-3	RA4015-6	RA4015-9
Consumption		20W	40W	60W
Input		Auto-sensing 100V or 240V AC at 50 or 60Hz via IEC cord		

Temperature Sensor	
Temperature Port	1 x temperature sensor port (sensor bundled)
Measurement Range	0 to 99.9°C
Measurement Accuracy	+/- 1.5%
Temperature Alarm	Yes

Environment	
Operating	0 to 50°C
Storage	-5 to 60°C
Relative Humidity	90%, non-condensing
Shock	50G acceleration (11ms, half-sine wave)
Vibration	58-100Hz / 0.98G (11ms / cycle)


Compliance	
EMC	FCC & CE certified
Safety	CE / LVD certified
Environment	RoHS2 & REACH compliant



RA4015-3



RA4015-6



Server Rack

