

RA4015-R 1U Rackmount 3 / 6 / 9 Fan Remote Trays

Intelligent (Remote) 1U Fan Tray



RA4015-9-R



Benefits

- ▶ 1U rackmount w/ 3, 6 or 9 fans
- ▶ Cascade ports for daisy chain up to 16 levels via Cat6 cable
- ▶ Designed for low noise & high airflow performance
- ▶ 1 x intelligent master fan unit allows access to 16 fan unit levels over internet
- ▶ Free management software remote access up to 480 fan units
- ▶ Auto & manual CFM setting reduces power consumption
- ▶ 1 x bundled temp. sensor with 2M wire
- ▶ Temperature sensing technology adjusts the fan speeds accordingly
- ▶ Unit or individual fan on / off (remote or local)
- ▶ 48V, 24V or 12VDC power option

Product Specifications

Intelligent Slave Fan	RA4015-3-R	RA4015-6-R	RA4015-9-R
No. of Fan	3	6	9
Mounting	1U	1U	1U
Unit CFM (approx.)	324 CFM	648 CFM	972 CFM
Individual Fan CFM		108 CFM	
Individual Fan ON / OFF		Yes	
CFM Level		Normal / High / Max.	
IP Remote Access	Not available, must be via Intelligent Master Fan on level 1		
Daisy Chain Level		for level 2 - 16	
MTBF		50,000 hrs	
Individual Fan Noise Level		41 dB	

Physical		RA4015-3-R	RA4015-6-R	RA4015-9-R
Dimensions (W x D x H)	Product	480 x 298 x 44 mm	480 x 458 x 44 mm	480 x 623 x 44 mm
		18.9 x 11.7 x 1.73 inch	18.9 x 18 x 1.73 inch	18.9 x 24.5 x 1.73 inch
Weight	Net	4 kg / 8.8 lb	6.8 kg / 15 lb	9 kg / 19.8 lb
Casing Color		Black		

Power	RA4015-3-R	RA4015-6-R	RA4015-9-R
Consumption	20W	40W	60W
Input	Auto-sensing 100V or 240V AC at 50 or 60Hz via IEC cord		

Temperature Sensor	
Temperature Port	1 x temperature sensor port (sensor bundled)
Measurement Range	0 to 99.9°C
Measurement Accuracy	+/- 1.5%
Temperature Alarm	Yes

Environment	
Operating	0 to 50°C
Storage	-5 to 60°C
Relative Humidity	90%, non-condensing
Shock	50G acceleration (11ms, half-sine wave)
Vibration	58-100Hz / 0.98G (11ms / cycle)


Compliance	
EMC	FCC & CE certified
Safety	CE / LVD certified
Environment	RoHS2 & REACH compliant




RA4015-3-R



RA4015-6-R



Front View



- Temp. port
- Daisy chain LINK port
- Daisy chain OUT port

Server Rack

