

# ID-E30Pw 30" High Resolution Widescreen LCD Panel Display

## Universal open frame mounting



FC CE


## Display Benefits

- ▶ 30" ultra widescreen LCD with 2560 x 1600 native **WQXGA** resolution
- ▶ PIP & Picture by Picture viewing efficiency
- ▶ Green LED-backlit panel technology
- ▶ 10-bit LCD delivers 1.07 billion true color
- ▶ Standard with Display port, HDMI, Dual-link DVI-D, VGA & remote controller

## Options

- MIL-type or lockable connector
- 48V or 24VDC power

## Basic I/O



## Specifications

### • LCD Panel

Manufacturer :	<b>LG</b>
Size (diagonal) :	30" Widescreen TFT
Max resolution :	2560 x 1600
Brightness (cd/m2) :	350
Backlight :	LED
Colors :	1.07 Billion, 10-bit
Contrast ratio (typ) :	1000 : 1
Viewing angle (H/V) :	178° x 178°
Active area (mm) :	641 x 401
MTBF (hrs) :	30,000
Signal input :	Display Port 1.2 / HDMI 1.4 / Dual-link DVI-D / VGA

### • Weight

Net : 11.9 kgs ( 26.2 lbs )

### • Mounting :

Universal mount / VESA mount

### • Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration ( 11 ms duration )
Vibration :	5~500Hz 1G RMS random vibration

### • Casing Color :

Black ( RAL 9005 )

### • Regulatory

Safety : FCC & CE certified

### • Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 70 Watt, Standby 5 Watt

### • Dimensions

Product : 740.9 x 71.5 x 500.4 mm / 29.2 x 2.8 x 19.7 inch

## Diagrams ( mm )

### Front View

### Side View

### Rear View

