




**Drawer Features & Display Benefits**

- ▶ 1U 19" widescreen LCD drawer with DVI-D / VGA input
- ▶ Short depth design of 460mm ( 18.1" )
- ▶ Green LED-backlit panel technology
- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed
- ▶ Enhanced aesthetics with molded front panel and two point lock

**Options**

- 3G / HD / SD-SDI Broadcast-grade input
- S-Video + Composite ( BNC )
- HDMI or Audio input
- 48V, 24V or 12VDC power



Standard I/O : VGA and DVI-D

Options I/O : HDMI, Audio, S-Video + BNC  
SDI

\*\* For the above options, casing depth will be extended from 460mm ( 18.1" ) to 530mm ( 20.9" )

**Specifications**

• LCD Panel

- Manufacturer :
- Size (diagonal) : 19" widescreen TFT
- Max resolution : 1440 x 900
- Brightness (cd/m2) : 250
- Backlight : LED
- Colors : 16.7M
- Contrast ratio (typ) : 1000 : 1
- Viewing angle (H/V) : 160° x 160°
- Active area (mm) : 408 x 255
- MTBF (hrs) : 30,000
- Signal input : VGA or DVI-D

• Casing Color : Black ( RAL 9005 )

• Weight

- Net : 12.5 kgs  
( 28 lbs )

• Environmental

- Operating : 0 to 50°C Degree
- Storage : -5 to 60°C Degree
- Relative humidity : 5~90%, non-condensing
- Shock : 10G acceleration ( 11 ms duration )
- Vibration : 5~500Hz 1G RMS random vibration

• Regulatory : FCC, CE

• Power

- Input : Auto-sensing 100 to 240VAC, 50 / 60Hz
- Consumption : Max. 48 Watt, Standby 5 Watt

• Dimensions

- Product : 441.6 x 460 x 44 mm / 17.4 x 18.1 x 1.73 inch

**Diagrams ( mm )**

