

# LCDR7U19-07 7U 19" 16:10 FORMAT MONITOR

( MADE IN U.S.A. )



- Mounts in 7U of 19" rack space.
- Wide format 16:10 aspect ratio.
- Fast 5 ms response time.
- 19" TFT LCD display with 1440 x 900 resolution.
- Analog (ARGB) and Digital (DVI-D) input connectors.
- Energy saving LED backlight.

## GENERAL SPECIFICATIONS

- Dimensions:**  
19.0" (W) x 12.25" (H) x 2.4" (D)
- Weight:**  
8.5 lbs.
- Power:**  
100 - 240 VAC, 50/60 Hz.  
20 Watts.
- On-Screen Controls:**  
Brightness, Contrast, Horizontal & Vertical  
Position, Auto Adjust, OSD H & V Position, Input Select  
Color Temp., Reset.
- Plug & Play:**  
DDC2B
- Temperature:**  
Operating: 10°C to 40°C  
Storage: -20°C to 45°C
- Humidity:**  
Operating: 10 to 80% RH (max)
- Input Signal (VGA):**  
R.G.B. analog video, TTL H & V sync.
- Input Signal (Digital):**  
DVI
- Input Connectors:**  
Analog: 15-pin mini D-Sub.  
Digital: 24 pin DVI-D.
- Colors Available:**  
Black.

## DISPLAY SPECIFICATIONS

- |   |   |
|---|---|
| <b>Display Type:</b><br>Active matrix TFT LCD             | <b>Viewing Angle:</b><br>Horizontal: 170°<br>Vertical: 160° |
| <b>Display area:</b><br>19" Wide.                         | <b>Response Time:</b><br>5 ms.                              |
| <b>Colors Displayed:</b><br>16.7 million colors.          | <b>Resolution:</b><br>Up to 1440 x 900.                     |
| <b>Contrast Ratio:</b><br>1,000:1 (Mega Infinity Dynamic) | <b>Aspect Ratio:</b><br>16:10.                              |
| <b>Brightness:</b><br>250 cd/m <sup>2</sup> typ.          | <b>Backlight type:</b><br>LED TN                            |
| <b>EPEAT</b><br>Gold                                      |   |

Specifications subject to change without notice.

## MODEL NUMBER

**LCDR7U19-07**

**LCDR7U19-07-Lex** with Lexan™ Screen Protection

*Contact us about other options and  
our additional rack mount products.*

